

# VersaTREK®

## Instrument Specifications

### 528 Model

Height .....	76 1/4 in.; 194 cm
Width .....	52 in.; 132 cm
Depth .....	30 3/4 in.; 78 cm
Weight (without bottles) .....	1,212 lbs; 561 kg
Distributed load* (528-22 with bottles) .....	132 lbs/ft <sup>2</sup> ; 644 kg/m <sup>2</sup>
Heat emission .....	2,307 BTU/hr



### 240 Model

Height .....	40 1/4 in.; 103 cm
Width .....	52 in.; 132 cm
Depth .....	30 3/4 in.; 78 cm
Weight .....	656 lbs; 304 kg
Distributed load* (240-10; with bottles) .....	70 lbs/ft <sup>2</sup> ; 339 kg/m <sup>2</sup>
Distributed load* (240-10; without bottles) .....	59 lbs/ft <sup>2</sup> ; 290 kg/m <sup>2</sup>
Heat emission .....	1,495 BTU/hr

### 240 Model with Cart

Height .....	40 1/4 in.; 103 cm
Height (on cart) .....	76 in.; 193 cm
Width .....	52 in.; 132 cm
Depth .....	30 3/4 in.; 78 cm
Weight (with cart, without bottles) .....	1,201 lbs; 545 kg
Distributed load* (240-10 cart with bottles) .....	119 lbs/ft <sup>2</sup> ; 580 kg/m <sup>2</sup>
Distributed load* (240-10 cart without bottles) .....	109 lbs/ft <sup>2</sup> ; 531 kg/m <sup>2</sup>
Heat emission .....	1495 BTU/hr
VersaTREK 240 Cart .....	Product # 6020-30



\*Distributed load refers to the force that the unit exerts across its "foot print" (width x depth), measured in pound-force per square foot (kilogram-force per square meter).

# VersaTREK®

## Clearance requirements (240 and 528 models)

Front .....	48 in.; 122 cm
Rear .....	4 in.; 11 cm
Top.....	24 in.; 61 cm
Side.....	4 in.; 11 cm

## Environmental (240 and 528 models)

Operating temperature.....	59° F to 82° F; 15° C to 28° C
Humidity (non-condensing).....	10% to 90%
Operating elevation (maximum).....	9842 feet; 3000 meters

## Electrical

### **240 Unit**

Line Voltage.....	110/240 vAC +/- 10%
Line Frequency.....	50/60 Hz +/- 5%
Wattage .....	700 watts (typical)

### **528 Unit**

Line Voltage.....	110/240 vAC +/- 10%
Line Frequency.....	50/60 Hz +/- 5%
Wattage .....	1200 watts (typical)

## Certifications (240 and 528 models)

UL.....	3101-1
CSA .....	22.2 No. 1010.1
IEC.....	61010-1:90 + A1:92 + A2:95
IEC.....	61326-1, 2002

## VersaTREK Windows® Software

VersaTREK Computer Package*.....	6110-31
----------------------------------	---------

\* The VersaTREK Computer Package includes 15" Touch Screen Monitor, Microsoft Access XP, VersaTREK Windows Software CD, HP Laserjet Printer, UPS 1200 VA Universal 6-Outlet, and VersaTREK Operator's CD Manual.

## TREK's Media Accessories

VersaTREK Myco Adaptors, 25/box.....	6040-30	Absorbent Sheet, each*.....	6444-30
Red Disable Location Cap, each*.....	6044-30	Label, Drawer, Numbered 1 - 22, each*..	6452-30
VersaTREK Stylus, 3/pack*.....	6420-30	VersaTREK EZ-ID Labels, 100/pack.....	6450-35
Bottle Carry Rack, 24-positions*.....	6424-30	Mounts, Thermometer, each*.....	6705-30
Thermometer, 18°C - 60°C, 125mm, each*.....	6440-30	VersaTREK Connectors, 50/box.....	7150-44

\* These items are included in the VersaTREK Starter Kit (6499-31). Quantities of these items in the Starter Kit are: 5 red disable location caps, 1 VersaTREK stylus 3-pack, 1 bottle carry rack, 3 thermometers, 3 absorbent sheets, 1 set of drawer labels, and 6 thermometer mounts. One cable, CAT5E 25' Snagless Patch (6172-30), is also included with the Starter Kit. One complete Starter Kit is shipped with each VersaTREK instrument.

## **Bottle Capacity — 240 Model**

Configuration	Number of Drawers	Maximum Annual Bottle Volume — 5 Day Blood Culture	Maximum Annual Bottle Volume — 7 Day Blood Culture	Maximum Annual Bottle Volume — Myco	Product Number
96	4	7,000	5,000	850	6240-04
144	6	12,500	7,500	1,250	6240-06
192	8	14,000	10,000	1,650	6240-08
240	10	17,500	12,500	2,100	6240-10

## **Bottle Capacity — 528 Model**

336	14	24,500	17,500	2,950	6528-14
384	16	28,000	20,000	3,350	6528-16
432	18	31,500	22,500	3,750	6528-18
480	20	35,000	25,000	4,200	6528-20
528	22	38,500	27,500	4,600	6528-22

